

GTEM 750

GTEM CELL FOR EMISSIONS AND IMMUNITY TESTING



GTEM 750, door right side

- Emissions and immunity testing in a single, shielded environment
- Meets basic standard: IEC/EN 61000-4-20
- Meets standards for emissions testing: CISPR 14-1, IEC 61000-6-3 and IEC 61000-6-4 for EUTs without connected cables
- Meets standards for immunity testing: EN 60118-13
- Ideal for design qualification and pre-certification
- Fields generated are largely homogeneous and simple to calculate
- Efficient power conversion requires smaller power amplifier
- Excellent VSWR over the entire frequency range - no need for measurement of reflected power

A GTEM (Gigahertz Transverse Electro Magnetic) cell is a test site for efficiently performing both radiated immunity and emissions testing in a single, controllable and shielded environment. Compared to other test sites, GTEM testing is faster with high accuracy and excellent reproducibility.

In principle, the GTEM cell is a coaxial line expanding pyramidally and having an impedance of 50 Ω. At its end, the line is terminated by a combination of termination resistors and RF absorbers designed and constructed to match the above mentioned impedance.

The GTEM 750 has a maximum septum height of 750 mm and is suitable for emissions and immunity testing.

Standard configuration:


- Under-carriage with locking casters and additional supports
- Door, left or right side, clear opening of 65 cm x 50 cm
- Shielded window in door, 30 cm x 10 cm
- Door contact for free application
- EUT BOX-1 with 2x 16 A filter, 1 socket inside, line safety switch, earth leakage circuit breaker, switchable illumination
- Media interface (Media S) for 3x N-type connectors and optical feed through
- Emission correlation tool (Windows software for manual input)
- Measurement report for TDR and VSWR
- Measurement report for input power requirements for 10 V/m (80 - 1000 MHz)
- Shipped disassembled, required Teseq supervisor, option ASS 750

Options:

- POW, extended version for 500 W RF-input power
- Special filter solutions
- SSA 750, stainless steel angles option for GTEM 750, recommended for countries with high humidity like Thailand, Malaysia, Philippines...
- Additional door
- XYZ manipulator MPH 600 handoperated or MPC 600 remote controlled
- Test house software for emission and immunity testing

Ordering information:

The door side and the country version of the single phase AC socket needs to be selected.



Schuko




UK version



US/JP version

GTEM 750

GTEM CELL FOR EMISSIONS AND IMMUNITY TESTING



Specifications

Max. septum height:	750 mm
Septum height at marker position:	650 mm
Dimension (LxWxH) in m:	3.95 x 2.02 x 1.95
Weight:	approx. 390 kg
Height H ₁ of cell corpus:	1.38 m
Height H ₂ of under-carriage:	0.57 m
Door (clear opening, LxH) in m:	0.65 x 0.50
EUT max. dimension (LxWxH) in m:	0.62 x 0.62 x 0.49
EUT dimension for uniform-area 0 to 6 dB (LxWxH) in m:	0.25 x 0.25 x 0.25
RF input connector:	N-type
Nominal impedance:	50 Ω
Frequency range:	DC up to 20 GHz
Frequency range according IEC/EN 61000-4-20:	30 to 1000 MHz
Return loss / VSWR (DC to 18 GHz):	>15 dB / <1.45:1
Shielding effectiveness (30 MHz to 3 GHz):	>60 dB (typ. >80 dB)
Max input power:	200 W (500 W with option POW)
Required input power for 10 V/m (isotropic, 5 points, 80 to 1000 MHz):	5.5 W (1.7 W CW)
Field deviation (isotropic, 5 points, 30 to 1000 MHz):	<6 dB

Model No. and options

Part number	Description
250200	GTEM 750 Septum height 750 mm, under-carriage, door, window, EUT BOX-1 and Media S included
251700	POW Extended version for 400 W (GTEM 500) or 500 W (GTEM 750) RF-input, switchable fans, order only with the device
251751	SSA 750 Stainless steel angles option for GTEM 750, recommended for countries with high humidity like Thailand, Malaysia, Philippines...
240380	ASS 750 Supervisor build up for GTEM 750 (travel and accommodation costs are additionally)
238405	MPH 600 Manipulator handoperated for GTEM 750

GTEM 750

GTEM CELL FOR EMISSIONS AND IMMUNITY TESTING

Model No. and options (continued)

240605	MPC 600 Manipulator remote controlled for GTEM 750
251930	SHD 3 Additionally shielded door, clear opening 0.65 m x 0.50 m
251100	EUT BOX-1 EUT supply for single phase, 2x 16 A filter, 1 socket inside, line safety switch, earth leakage circuit breaker, switchable illumination, available for GTEM 500 to 2000
251200	EUT BOX-3 EUT supply for three phase, 4x 32 A filter, 1 socket inside, line safety switch, earth leakage circuit breaker, switchable illumination, available for GTEM 500 to 2000
251201	EUT BOX-31 Option for GTEM 500 - 2000: Upgrade of EUT BOX-1 (included in standard delivery) to EUT BOX-3, order only with GTEM
251210	EUT BOX-4 Option for GTEM 500 - 2000: EUT Box with DC power filter 4x 10 A, banana jacks 4 mm
251000	DC1 Option for EUT BOX-1, EUT BOX-3 or EUT BOX-31: DC power filter 2x 10 A, banana jacks 4 mm
251820	SIF M 25 lines signal filter for Media, 5 A, D sub 25 pins
248290	ITE Filter Filter for 2 balanced pairs with adapters for RJ11 and RJ45 (ADR T411, ADR T442, ADR T443 and ADR T444)
248270	CAN Filter Filter for 6 lines CAN bus, D sub 9 pins
248375	RS232 Filter 9 lines signal filter, 5 A, D sub 9 pins
248382	USB Filter Filter for shielded USB
251600	Media S Connector panel with frame, 3x N-type connectors, 1x optical feed through
251650	Plate S Exchange panel for media S

AMETEK CTS Europe GmbH
Landsberger Str. 255 · 12623 Berlin · Germany
T +49 30 56 59 88 35 F +49 30 56 59 88 34
info.rf.cts@ametek.com www.ametek-cts.com

© November 2017 Teseq®
Specifications subject to change without notice.
Teseq® is an ISO-registered company. Its products are designed and manufactured under the strict quality and environmental requirements of the ISO 9001. This document has been carefully checked. However, Teseq® does not assume any liability for errors or inaccuracies.

82-250200 E02 November 2017